



## Main

|                               |   |
|-------------------------------|---|
| Range of product              | Harmony XB4   |
| Product or component type     | Complete body/light block assembly                            |
| Device short name             | ZB4   |
| Fixing collar material        | Zamak   |
| Sale per indivisible quantity | 1   |
| Connections - terminals       | Faston connector(1 x 6.35 mm)<br>Faston connector(2 x 2.8 mm) |
| Light source                  | Incandescent  |
| Bulb base                     | BA 9s   |
| Light block supply            | Via integral transformer, 1.2 VA - 6 V                        |
| [Us] rated supply voltage     | 440...480 V AC, 50/60 Hz                                      |

## Complementary

|  |   |
|--|---|
| CAD overall width                      | 1.18 in (30 mm)   |
| CAD overall height                     | 1.85 in (47 mm)   |
| CAD overall depth                      | 2.36 in (60 mm)   |
| Terminals description ISO n°1          | (X1-X2)PL   |
| [Ui] rated insulation voltage          | 250 V (degree of pollution: 3) conforming to EN 60947-1 |
| [Uimp] rated impulse withstand voltage | 4 kV conforming to EN 60947-1                           |
| Signalling type                        | Steady  |
| Mounting of block                      | Front mounting  |
| Electrical composition code            | P4<br>M9  |

## Environment

|                                       |                                 |
|---------------------------------------|---------------------------------|
| Protective treatment                  | TH                              |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C)      |
| Ambient air temperature for operation | -40...131 °F (-40...55 °C)      |
| Electrical shock protection class     | Class I conforming to IEC 60536 |
| IP degree of protection               | IP20                            |
| Standards                             | JIS C 4520<br>EN/IEC 60947-5-5  |

EN/IEC 60947-5-4  
EN/IEC 60947-5-1  
UL 508  
CSA C22.2 No 14  
EN/IEC 60947-1

---

|                        |  |
|------------------------|--|
| Product certifications | CSA<br>UL listed   |
| Vibration resistance   | 5 gn (f = 2...500 Hz) conforming to IEC 60068-2-6  |
| Shock resistance       | 30 gn (duration = 18 ms) half sine wave acceleration conforming to IEC 60068-2-27<br>50 gn (duration = 11 ms) half sine wave acceleration conforming to IEC 60068-2-27 |

---

### Offer Sustainability

---

|                           |  |
|---------------------------|--|
| California proposition 65 | WARNING: This product can expose you to chemicals including:   |
| ----- Substance 1         | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| ----- More information    | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                    |

---

### Contractual warranty

---

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

---