

# Product data sheet

## Characteristics

# XUDA2NSMM8

photoelectric sensor - fiber optic amplifier - NO/  
NC programmable - M8 connector

Product availability : Non-Stock - Not normally stocked in distribution facility

Price\*\* : 210.00 USD



### Main

Range of product	OsiSense XU
Series name	Application assembly
Specific application of photoelectric detector	Object
Sensor name	XUD

### Complementary

Electronic sensor type	Photo-electric sensor
Sensor design	Fiber design
Enclosure material	PBT
Wiring technique	3-wire
Supply circuit type	DC
Type of output signal	Discrete
Output type	Solid state
Discrete output function	1 NO or 1 NC programmable
Discrete output type	NPN
Electrical connection	1 male connector M8, 4 pins
Cable material	PVC
Status LED	Stability 1 LED green) Output state 1 LED yellow)
[Us] rated supply voltage	12...24 V DC reverse polarity protection
Supply voltage limits	10.8...26.4 V DC
Current consumption	<= 50 mA no-load
Switching capacity in mA	<= 100 mA overload protection) <= 100 mA short-circuit protection)
Maximum voltage drop	<1 V closed)
Time delay range	0...40 s
Switching frequency	<= 1 kHz <= 5 kHz
Add on output	With alarm output, 50 mA overload protection With alarm output, 50 mA short-circuit protection

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum delay first up	120 ms
Maximum delay response	0.1 ms
Maximum delay recovery	0.1 ms
Product compatibility	Glass or plastic fibre optics 1 mm or 2.2 mm
Setting-up	Sensitivity adjustment with teach mode
Display type	4-digit
Lens material	PMMA
Depth	0.39 in (10 mm)
Height	2.56 in (65 mm)
Width	1.57 in (40 mm)
Net weight	0.09 lb(US) (0.04 kg)

## Environment

Emission	Red
Interference protection	With
Product certifications	CULus CE
IP degree of protection	IP64 optic fiber Ø 1 mm IEC 529 IP65 optic fiber Ø 2 mm IEC 529
Ambient air temperature for operation	14...131 °F (-10...55 °C)
Ambient air temperature for storage	-22...158 °F (-30...70 °C)
Vibration resistance	+/-0.5 mm 10...55 Hz)IEC 60068-2-6 7 gn 10...55 Hz)IEC 60068-2-6
Shock resistance	30 gn 11 ms) IEC 60068-2-27

## Ordering and shipping details

Category	22481 - SENSORS, PHOTOELECTRIC
Discount Schedule	DS2
GTIN	00785901700203
Package weight(Lbs)	0.04 kg (0.09 lb(US))
Returnability	No
Country of origin	HU

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP) and Diisononyl phthalate (DINP) which is known to the State of California to cause Carcinogen + Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------