

# Product data sheet

## Characteristics

# XULA700115K

photo-electric sensor - XUL - diffuse - Sn 0.7m - 24..240VAC/DC - 1/2"

Product availability : Non-Stock - Not normally stocked in distribution facility

Price\* : 123.00 USD



### Main

Range of product	OsiSense XU
Series name	General purpose single mode
Electronic sensor type	Photo-electric sensor
Sensor name	XUL
Sensor design	Compact
Detection system	Diffuse
Material	Plastic
Type of output signal	Discrete
Supply circuit type	AC/DC
Wiring technique	2-wire
Discrete output function	1 NC
Electrical connection	1 male connector 1/2"20 UNF, 3 pins
Product specific application	-
Emission	Infrared diffuse
[Sn] nominal sensing distance	2.3 ft (0.7 m) diffuse

### Complementary

Enclosure material	ABS/PC
Lens material	PMMA
Maximum sensing distance	2.95 ft (0.9 m)
Output type	Solid state
Output function governance	Light
Add on output	Without
Cable composition	2 x 0.34 mm <sup>2</sup>
Wire insulation material	PVC
Cable outer diameter	0.24 in (6 mm)
Status LED	1 LED output state
[Us] rated supply voltage	24...240 V AC/DC
Supply voltage limits	20...264 V AC/DC
Residual current	< 1.5 mA (open state) AC/DC

Switching capacity in mA	<= 3000 mA (inrush mode, to be used with 0.63 A quick-blow fuse in series with the load) >= 5 mA (sealed mode, to be used with 0.63 A quick-blow fuse in series with the load)
Switching frequency	<= 20 Hz
Voltage drop	<= 10 V (closed state) (I = 5 mA) <= 3 V (closed state) (I = 0.1...0.5 A) <= 5.5 V (closed state) (I = 10 mA)
Delay first up	<= 300 ms
Delay response	<= 20 ms
Delay recovery	<= 20 ms
Setting-up	Without sensitivity adjustment
Depth	1.38 in (35 mm)
Height	2.76 in (70 mm)
Width	0.71 in (18 mm)
Product weight	0.3 lb(US) (0.135 kg)
Kit composition	Sensor Bracket XULZ41

## Environment

Product certifications	CE
Ambient air temperature for operation	-13...140 °F (-25...60 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)
Vibration resistance	7 gn, amplitude = +/- 2 mm (f = 10...55 Hz) conforming to IEC 60068-2-6
Shock resistance	20 gn (duration = 11 ms) conforming to IEC 60068-2-27
IP degree of protection	IP651 conforming to NF C 20-010 IP65 conforming to IEC 60529

## Ordering and shipping details

Category	22481 - SENSORS, PHOTOELECTRIC
Discount Schedule	DS2
GTIN	00785901920007
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5100000000000001
Returnability	N
Country of origin	FR

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2013 <a href="#">Will be compliant on 3Q2013</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------