

Product data sheet

Characteristics

XULK0830D

photo-electric sensor - XUL - emitter - 12..24VDC
- M12

Product availability : Non-Stock - Not normally stocked in distribution facility

Price* : 47.70 USD



Main

Range of product	OsiSense XU
Series name	General purpose single mode
Electronic sensor type	Photo-electric sensor transmitter
Sensor name	XUL
Sensor design	Compact
Detection system	Thru beam
Material	Plastic
Supply circuit type	DC
Wiring technique	2-wire
Electrical connection	1 male connector M12, 4 pins
Emission	Infrared thru beam
[Sn] nominal sensing distance	26.25 ft (8 m) thru beam need a receiver

Complementary

Enclosure material	ABS
Lens material	PMMA
[Us] rated supply voltage	12...24 V DC with reverse polarity protection
Supply voltage limits	10...30 V DC
Current consumption	<= 35 mA
Delay first up	<= 15 ms
Setting-up	Without sensitivity adjustment
Depth	1.38 in (35 mm)
Height	2.76 in (70 mm)
Width	0.71 in (18 mm)
Product weight	0.3 lb(US) (0.135 kg)

Environment

Product certifications	CE
Ambient air temperature for operation	-13...131 °F (-25...55 °C)

Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Vibration resistance	7 gn, amplitude = +/- 2 mm (f = 10...55 Hz) conforming to IEC 60068-2-6
Shock resistance	20 gn (duration = 11 ms) conforming to IEC 60068-2-27
IP degree of protection	IP671 conforming to NF C 20-010 IP67 conforming to IEC 60529

Ordering and shipping details

Category	22481 - SENSORS, PHOTOELECTRIC
Discount Schedule	DS2
GTIN	00785901898788
Nbr. of units in pkg.	1
Package weight(Lbs)	0.20999999999999999
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2013 Will be compliant on 3Q2013
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------