

Price* : 1,856.00 USD



⚠ Discontinued

XUSLPZ3A0400B has not been replaced. Please contact your customer care center for more information.

Main

Range of product	Preventa Safety detection
Product or component type	Safety light curtain type 4
Device short name	XUSLP
Design	Compact
Detection system	Transmitter-receiver system
Product specific application	For body protection
Height protected	31.5 in (800 mm)
Minimum object diameter for detection	15.75 in (400 mm)
[Sn] nominal sensing distance	2.62...65.62 ft (0.8...20 m) depending on configuration 2.62...229.66 ft (0.8...70 m) depending on configuration
Response time	< 16 ms depending on light beam coding C < 20 ms depending on light beam coding B < 24 ms depending on light beam coding A
Number of beams	3
Type of receiver	Active

Complementary

Kit composition	1 receiver(s) 1 transmitter(s) 1 user guide with certificate of conformity 2 sets of 2 brackets with fixings
[EAA] effective aperture angle	2.5 ° at 3 m
Light source	GaAIAs LED, 850 nm
[Us] rated supply voltage	24 V DC (+/- 20 %)
[Ie] rated operational current	2 A
Current consumption	100 mA (transmitter) 300 mA no-load (receiver) 1.6 A with maximum load (receiver)
Output type	1 auxiliary output solid-state PNP 2 safety outputs OSSD solid-state PNP (NO) (short-circuit protection)
Output current limits	<= 100 mA for auxiliary output <= 650 mA for safety outputs OSSD
Output voltage	24 V
Output circuit type	DC

Switching capacity in mA	650 mA
Monitoring act of of relay MPCE/EDM	50 mA
Local signalling	1 LED (transmitter), function: power supply 3 LEDs (receiver), function: stop, run, interlock + 2 digit display
Electrical connection	Terminal block
Function available	Alignment aid by display of each light beam broken Auto, manual, manual 1st cycle Display of operating modes and alarm by LEDs and 2-digit display Monitoring of external switching devices Test
Marking	CE
Material	Casing : aluminium End caps : 20 % fibre glass impregnated nylon Front face : acrylic
Fixing mode	End brackets
Product weight	15.87 lb(US) (7.2 kg)

Environment

Standards	ANSI B11:19-1990 ANSI/RIA R15.06 EN/IEC 61496-1 EN/IEC 61496-1-2 for type 4 ESPE EN/IEC 61496-2 OSHA 1910-212 OSHA 1910-217C ROHS directive 2002/95/EC Machinery directive 2006/42/EC EMC 2004/108/EC Work equipment directive 2009/104/EC
Product certifications	CSA TÜV UL
Safety level	Type 4 conforming to IEC 61496-1-2 Can reach SIL 3 conforming to IEC 61508 (correctly wired) Can reach category 4 conforming to EN/ISO 13849-1 (correctly wired) Can reach PL = e conforming to EN/ISO 13849-1 (correctly wired)
Safety reliability data	PFH = 2.7E-9 1/h conforming to IEC 61508 (verified in worst case conf: 6 beams), proof test interval = 20 yr
Ambient air temperature for operation	32...131 °F (0...55 °C)
Ambient air temperature for storage	-13...167 °F (-25...75 °C)
Relative humidity	0...95 % without condensation
IP degree of protection	IP65 IP67
Shock resistance	10 gn 16 ms conforming to IEC 61496-1
Vibration resistance	0.35 +/- 0.05 mm (f = 10...55 Hz) conforming to IEC 61496-1

Ordering and shipping details

Category	22455 - LIGHT CURTAINS - XUSL
Discount Schedule	DS2
Nbr. of units in pkg.	1
Package weight(Lbs)	19
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0730 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------
