



Main

| | |
|-------------------------------|--|
| Range of product | Harmony XB4 |
| Product or component type | Head for illuminated double-headed push-button |
| Product compatibility | Integral LED |
| Device short name | ZB4 |
| Bezel material | Black metal |
| Head type | Standard |
| Mounting diameter | 0.87 in (22 mm) |
| Sale per indivisible quantity | 1 |
| Shape of signaling unit head | Rectangular |
| Type of operator | Spring return |
| Operator profile | 2 flush push-buttons - 1 central pilot light |
| Operators description | White "up arrow" - white "down arrow" |

Complementary

| | |
|------------------------------------|--|
| CAD overall width | 1.18 in (30 mm) |
| CAD overall height | 1.97 in (50 mm) |
| CAD overall depth | 1.18 in (30 mm) |
| Product weight | 0.12 lb(US) (0.056 kg) |
| Resistance to high pressure washer | 1015.26 psi (7000000 Pa) at 131 °F (55 °C), distance: 0.1 m |
| Colour of marking | Black marking when white caps White marking when green, red or black caps |
| Operator profile | White flush, black down arrow White flush, black up arrow |
| Mechanical durability | 1000000 cycles |
| Electrical composition code | M1 for 6 contacts using single blocks in front mounting with integral LED M2 for 6 contacts using single and double blocks in front mounting with integral LED M6 for 2 contacts using single blocks in front mounting with integral LED and transformer M10 for 2 contacts using single blocks in front mounting with integral LED |

Environment

| | |
|-------------------------------------|----------------------------|
| Protective treatment | TH |
| Ambient air temperature for storage | -40...158 °F (-40...70 °C) |

| | |
|---------------------------------------|---|
| Ambient air temperature for operation | -40...158 °F (-40...70 °C) |
| Electrical shock protection class | Class I conforming to IEC 61140 |
| IP degree of protection | IP69 IP66 conforming to IEC 60529 IP67 conforming to IEC 60529 IP69K |
| NEMA degree of protection | NEMA 13 NEMA 4X |
| IK degree of protection | IK06 conforming to IEC 50102 |
| Standards | EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 EN/IEC 60947-5-5 JIS C 4520 UL 508 CSA C22.2 No 14 |
| Product certifications | BV CSA DNV GL LROS (Lloyds register of shipping) RINA UL listed |
| Vibration resistance | 5 gn (f = 2...500 Hz) conforming to IEC 60068-2-6 |

Offer Sustainability

| | |
|---------------------------|--|
| California proposition 65 | WARNING: This product can expose you to chemicals including: |
| ----- Substance 1 | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| ----- More information | For more information go to www.p65warnings.ca.gov |

Contractual warranty

| | |
|-----------------|---------------------|
| Warranty period | 18 months 18 months |
|-----------------|---------------------|