Product data sheet

Specifications





Indicator bank, Harmony XVB, illuminated unit, plastic, yellow, 70mm, integral flash discharge tube, 5joule, 24V AC/DC

XVBC6B8

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 233.00 USD

Main

| Range Of Product | Harmony XVB Universal |
|---------------------------------------|---------------------------------------|
| Product Or Component Type | Indicator bank |
| Beacon Or Indicator Bank Unit Type | Illuminated unit |
| Signalling Type | Flashing |
| Mounting Diameter | 2.76 in (70 mm) |
| Component Name | XVBC |
| Material | Polycarbonate |
| Light Source | Integral flash discharge tube, yellow |
| Bulb Type | Flash discharge tube |
| [Us] Rated Supply Voltage | 24 V AC/DC |
| Flash Energy | 5 J |

Complementary

| Assembly Style | Customer assembly, up to 5 units |
|---|--|
| Connections - Terminals | Screw clamp terminals, <= 1 x 1.5 mm ² with cable end |
| [Ui] Rated Insulation Voltage | 250 V IEC 60947-1 |
| Nominal Voltage Limit | 0.851.1 Un IEC 60947-5-1 |
| Current Consumption | < 350 mA DC < 550 mA AC |
| [Uimp] Rated Impulse Withstand Voltage | 4 kV IEC 60947-1 |
| Flashing Frequency | 1 Hz |
| Cad Overall Width | 2.76 in (70 mm) |
| Cad Overall Height | 6.18 in (157 mm) |
| Cad Overall Depth | 2.76 in (70 mm) |
| Net Weight | 0.65 lb(US) (0.295 kg) |

Environment

Product Certifications

CCC EAC CSA C22-2 No 14 UL 508

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Standards | IEC 60947-5-1 |
|--|--|
| Protective Treatment | TC |
| Ambient Air Temperature For Storage | -40158 °F (-4070 °C) |
| Electrical Shock Protection Class | Class I on support tube IEC 61140 Class II on base unit IEC 61140 |
| Ip Degree Of Protection | IP65 on fixing base XVBZ0. IEC 60529 IP66 on base unit IEC 60529 |
| Nema Degree Of Protection | Type 4X UL indoor) |

Ordering and shipping details

| Category | US100XV22611 |
|-------------------|---------------|
| Discount Schedule | 00XV |
| Gtin | 3389110845655 |
| Returnability | No |
| Country Of Origin | FR |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------------|
| | |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.15 in (8 cm) |
| Package 1 Width | 3.86 in (9.8 cm) |
| Package 1 Length | 8.50 in (21.6 cm) |
| Package 1 Weight | 10.44 oz (296 g) |
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 12 |
| Package 2 Height | 11.81 in (30 cm) |
| Package 2 Width | 11.81 in (30 cm) |
| Package 2 Length | 15.75 in (40 cm) |
| Package 2 Weight | 8.88 lb(US) (4.027 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

| Reach Regulation | REACh Declaration | |
|---------------------------|--|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) | |
| China Rohs Regulation | China RoHS declaration | |
| Environmental Disclosure | Product Environmental Profile | |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. | |
| Circularity Profile | No need of specific recycling operations | |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov | |


Product data sheet

Dimensions Drawings

Indicator Bank with "Flash" Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get \mathbf{b} dimension.



- (1) Base unit XVBC07, to be ordered separately
- (2) Illuminated or audible signalling unit XVBC ..., to be ordered separately
- (3) "Flash" unit

| Number of illuminated or audible signalling units other than "flash" tube | b in mm | b in in. |
|---|---------|----------|
| 1 | 295 | 11.61 |
| 2 | 358 | 14.09 |
| 3 | 421 | 16.57 |
| 4 | 484 | 19.06 |