

# Product data sheet

Specifications



Indicator bank, Harmony XVB, illuminated unit, plastic, orange, 70mm, integral flash discharge tube, 10joule, 120V AC

XVBC8G5

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 314.00 USD

## Main

Range Of Product	Harmony XVB Universal
Product Or Component Type	Indicator bank
Beacon Or Indicator Bank Unit Type	Illuminated unit
Signalling Type	Flashing
Mounting Diameter	2.76 in (70 mm)
Component Name	XVBC
Material	Polycarbonate
Light Source	Integral flash discharge tube, orange
Bulb Type	Flash discharge tube
[Us] Rated Supply Voltage	120 V AC
Flash Energy	10 J

## Complementary

Assembly Style	Customer assembly, up to 5 units
Connections - Terminals	Screw clamp terminals, $\leq 1 \times 1.5 \text{ mm}^2$ with cable end
[Ui] Rated Insulation Voltage	250 V IEC 60947-1
Nominal Voltage Limit	0.85...1.1 Un IEC 60947-5-1
Current Consumption	$< 290 \text{ mA AC}$
[Uimp] Rated Impulse Withstand Voltage	4 kV IEC 60947-1
Flashing Frequency	1 Hz
Cad Overall Width	2.76 in (70 mm)
Cad Overall Height	6.18 in (157 mm)
Cad Overall Depth	2.76 in (70 mm)
Net Weight	0.69 lb(US) (0.315 kg)

## Environment

Product Certifications	CCC EAC CSA C22-2 No 14 UL 508
------------------------	---

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Standards</b>	IEC 60947-5-1
<b>Protective Treatment</b>	TC
<b>Ambient Air Temperature For Storage</b>	-40...158 °F (-40...70 °C)
<b>Electrical Shock Protection Class</b>	Class I on support tube IEC 61140 Class II on base unit IEC 61140
<b>Ip Degree Of Protection</b>	IP65 on fixing base XVBZ0. IEC 60529 IP66 on base unit IEC 60529
<b>Nema Degree Of Protection</b>	Type 4X UL indoor)

## Ordering and shipping details

<b>Category</b>	US100XV22611
<b>Discount Schedule</b>	00XV
<b>Gtin</b>	3389110845808
<b>Returnability</b>	No
<b>Country Of Origin</b>	CZ

## Packing Units

<b>Unit Type Of Package 1</b>	PCE
<b>Number Of Units In Package 1</b>	1
<b>Package 1 Height</b>	3.15 in (8.0 cm)
<b>Package 1 Width</b>	3.15 in (8.0 cm)
<b>Package 1 Length</b>	7.36 in (18.7 cm)
<b>Package 1 Weight</b>	11.11 oz (315.0 g)
<b>Unit Type Of Package 2</b>	S03
<b>Number Of Units In Package 2</b>	12
<b>Package 2 Height</b>	11.81 in (30.0 cm)
<b>Package 2 Width</b>	11.81 in (30.0 cm)
<b>Package 2 Length</b>	15.75 in (40.0 cm)
<b>Package 2 Weight</b>	9.91 lb(US) (4.493 kg)

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Mercury Free

Rohs Exemption Information Yes

## Certifications & Standards


Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

Dimensions Drawings

Indicator Bank with “Flash” Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get **b** dimension.



- (1) Base unit XVBC07, to be ordered separately
- (2) Illuminated or audible signalling unit XVBC\*\*\*, to be ordered separately
- (3) “Flash” unit

Number of illuminated or audible signalling units other than “flash” tube	b in mm	b in in.
1	295	11.61
2	358	14.09
3	421	16.57
4	484	19.06