

Product data sheet

Specifications



kit illuminated unit with light source for XVB tower light

XVBKEQ3743G3

⚠ Discontinued on: Jan 23, 2021

⚠ Discontinued

Main

Range Of Product	Harmony XVB Universal
Product Or Component Type	Indicator bank
Beacon Or Indicator Bank Unit Type	Illuminated unit
Signalling Type	Steady
Mounting Diameter	2.76 in (70 mm)
Component Name	XVBC
Material	Polycarbonate
Light Source	LED, green
Bulb Type	LED BA 15d
[Us] Rated Supply Voltage	<= 250 V

Complementary

Assembly Style	Customer assembly, up to 5 units
Maximum Power Dissipation In W	7 W
Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm ² with cable end
[Uimp] Rated Impulse Withstand Voltage	4 kV IEC 60947-1
Cad Overall Width	2.76 in (70 mm)
Cad Overall Height	2.48 in (63 mm)
Cad Overall Depth	2.76 in (70 mm)
Net Weight	0.31 lb(US) (0.14 kg)

Environment

Pollution Degree	2
Product Certifications	CCC EAC CSA C22-2 No 14 UL 508
Standards	EN/IEC 60947-5-1
Protective Treatment	TC
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...122 °F (-25...50 °C) LED -13...158 °F (-25...70 °C) incandescent

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical Shock Protection Class	Class I on support tube IEC 61140 Class II on base unit IEC 61140
Ip Degree Of Protection	IP65 on fixing base XVBZ0. IEC 60529 IP66 on base unit IEC 60529
Nema Degree Of Protection	Type 4X UL indoor)

Ordering and shipping details

Category	22611-XVB-STACKLIGHTS
Discount Schedule	XV
Gtin	00785901405801
Returnability	No
Country Of Origin	FR

Contractual warranty

Warranty	18 months
----------	-----------