# Product data sheet

Specification





Complete body/contact assembly and light block, Harmony XB5, blue with body/fixing collar with BA9s LED bulb 400 V 1NO+1NC

ZB5AW05D65



Discontinued on: May 6, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range Of Product	Harmony XB5				
Product Or Component Type	Complete body/contact assembly and light block				
Device Short Name	ZB5				
Fixing Collar Material	Plastic				
Sale Per Indivisible Quantity	1				
Head Type	Standard				
Contacts Type And Composition	1 NO + 1 NC				
Contact Operation	Slow-break				
Connections - Terminals	Screw clamp terminals, <= 2 x 1.5 mm <sup>2</sup> with cable end EN 60947-1 Screw clamp terminals, >= 1 x 0.22 mm <sup>2</sup> without cable end EN 60947-1				
Light Source	LED				
Bulb Base	BA 9s				
Light Block Supply	Via integral transformer 1.2 VA 6 V				
Light Source Colour	Blue				

### Complementary

Cad Overall Width	1.18 in (30 mm)
Cad Overall Height	1.65 in (42 mm)
Cad Overall Depth	3.11 in (79 mm)
Terminals Description Iso N°1	(11-12)NC (13-14)NO
Net Weight	0.26 lb(US) (0.119 kg)
Contacts Usage	Standard
Positive Opening	With EN/IEC 60947-5-1 appendix K
Operating Travel	0.06 in (1.5 mm) NC changing electrical state) 0.10 in (2.6 mm) NO changing electrical state) 0.17 in (4.3 mm) total travel)
Operating Force	2 N NC changing electrical state 2.3 N NO changing electrical state
Operating Torque	0.44 lbf.in (0.05 N.m) NO changing electrical state
Mechanical Durability	5000000 cycles

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Tightening Torque	7.0810.62 lbf.in (0.81.2 N.m) EN 60947-1				
Shape Of Screw Head	Cross Philips no 1				
	Cross pozidriv No 1				
	Slotted flat Ø 4 mm				
	Slotted flat Ø 5.5 mm				
Contacts Material	Silver alloy (Ag/Ni)				
Short-Circuit Protection	10 A cartridge fuse gG EN/IEC 60947-5-1				
[Ith] Conventional Free Air Thermal Current	10 A EN/IEC 60947-5-1				
[Ui] Rated Insulation Voltage	600 V 3)EN 60947-1				
[Uimp] Rated Impulse Withstand Voltage	6 kV EN 60947-1				
[le] Rated Operational Current	3 A 240 V, AC-15, A600 EN/IEC 60947-5-1				
	6 A 120 V, AC-15, A600 EN/IEC 60947-5-1				
	0.1 A 600 V, DC-13, Q600 EN/IEC 60947-5-1				
	0.27 A 250 V, DC-13, Q600 EN/IEC 60947-5-1				
	0.55 A 125 V, DC-13, Q600 EN/IEC 60947-5-1				
	1.2 A 600 V, AC-15, A600 EN/IEC 60947-5-1				
Electrical Durability	1000000 cycles, AC-15, 2 A 230 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C				
	1000000 cycles, AC-15, 3 A 120 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C				
	1000000 cycles, AC-15, 4 A 24 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C				
	1000000 cycles, DC-13, 0.2 A 110 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C				
	1000000 cycles, DC-13, 0.5 A 24 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C				
Electrical Reliability	Λ < 10exp(-6) 5 V 1 mA in clean environment EN/IEC 60947-5-4				
	$\Lambda$ < 10exp(-8) 17 V 5 mA in clean environment EN/IEC 60947-5-4				
Signalling Type	Steady				
[Us] Rated Supply Voltage	400 V AC 50/60 Hz				

## **Environment**

Protective Treatment	тн
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Electrical Shock Protection Class	Class II IEC 60536
Standards	CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-1 JIS C8201-5-1 UL 508 EN/IEC 60947-5-4 JIS C8201-1
Product Certifications	CSA DNV GL LROS (Lloyds register of shipping) UL Listed BV
Vibration Resistance	5 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27

# Ordering and shipping details

Category	US10CS222467
Discount Schedule	0CS2
Gtin	3389110909661
Returnability	No

Country Of Origin FR

## **Contractual warranty**

Warranty 18 months

# Sustainability Screen Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**


Reach Regulation	REACh Declaration					
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)					
China Rohs Regulation	China RoHS declaration					
<b>Environmental Disclosure</b>	Product Environmental Profile					
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.					
Weee Circularity Profile	· · · · · · · · · · · · · · · · · · ·					

# **Product data sheet**

## **ZB5AW05D65**

## **Dimensions Drawings**


### **Dimensions**



#### Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


#### Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) Ø22.5 mm recommended (Ø22.3  $_0^{+0.4}$ ) / Ø0.89 in. recommended (Ø0.88 in.  $_0^{+0.016}$ )

			•	
Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	30	1.18
By Faston connectors	45	1.77	32	1.26
On printed circuit board	30	1.18	30	1.18

#### **Detail of Lug Recess**



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) Ø22.5 mm recommended (Ø22.3  $_0^{+0.4}$ ) / Ø0.89 in. recommended (Ø0.88 in.  $_0^{+0.016}$ )