# **Product data sheet**

Specification





Head for illuminated push button, Harmony XB5, plastic, green flush, 22mm, universal LED, plain lens, clear boot

ZB5AW533

Product availability: Stock - Normally stocked in distribution facility

Important message: A change in appearance may be noted on the product but does not affect its use in terms of function and safety. This makes it compatible with our Universal LED blocks

Price\*: 31.00 USD

#### Main

Range Of Product	Harmony XB5	
Product Or Component Type	Head for illuminated push-button	
Device Short Name	ZB5	
Product Compatibility	Universal LED	
Bezel Material	Dark grey plastic	
Mounting Diameter	0.87 in (22 mm)	
Sale Per Indivisible Quantity	1	
Head Type	Standard	
Shape Of Signaling Unit Head	Round	
Type Of Operator	spring return	
Operator Profile	Green flush, unmarked	
Operator Additional Information	Clear boot	

# Complementary

Cad Overall Width	1.18 in (30 mm)	
Cad Overall Height	1.18 in (30 mm)	
Cad Overall Depth	1.46 in (37 mm)	
Net Weight	0.04 lb(US) (0.019 kg)	
Resistance To High Pressure Washer	1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m	
Mechanical Durability	10000000 cycles	
Main Group	Illum push-button	
Group Of Product	Flush push integral LED	
Station Name	XALD 15 cut-outs XALK 25 cut-outs	
Cap/Operator Or Lens Colour	Green	
Marking	Unmarked	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Electrical Composition Code</b>	M1 6 single front mounting integral LED		
	M2 6 single and double front mounting integral LED		
	M6 2 single front mounting integral LED and transformer		
	M10 2 single front mounting integral LED		
	MF1 2 single front mounting integral LED		
	MR1 2 single rear mounting integral LED		
Device Presentation	Basic sub-assemblies		

# **Environment**

Protective Treatment	TC			
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)			
Ambient Air Temperature For -40158 °F (-4070 °C)  Operation				
Overvoltage Category Class II IEC 60536				
Ip Degree Of Protection	Protection IP66 IEC 60529 IP67			
Nema Degree Of Protection	NEMA 13 NEMA 4X			
Ik Degree Of Protection IK05 conforming to EN 50102				
Standards	JIS C8201-5-1 EN/IEC 60947-1 CSA C22.2 No 14 UL 508 EN/IEC 60947-5-4 GB 14048.5 EN/IEC 60947-5-1 JIS C8201-1			
Product Certifications	CSA BV GL DNV UL Listed LROS (Lloyds register of shipping)			
Vibration Resistance	5 gn 2500 Hz)IEC 60068-2-6			
Shock Resistance 30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27				

# Ordering and shipping details

Category	US10CS222467
Discount Schedule	0CS2
Gtin	3389110924046
Returnability	Yes
Country Of Origin	MX

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.57 in (4.0 cm)
Package 1 Width	1.89 in (4.8 cm)
Package 1 Length	1.02 in (2.6 cm)
Package 1 Weight	0.71 oz (20.0 g)
Unit Type Of Package 2	S03

Number Of Units In Package 2	300
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	14.71 lb(US) (6.671 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

# Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**


Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			

# **Product data sheet**

# **ZB5AW533**

**Dimensions Drawings** 


# **Dimensions**



#### Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


#### Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) Ø22.5 mm recommended (Ø22.3  $_0^{+0.4}$ ) / Ø0.89 in. recommended (Ø0.88 in.  $_0^{+0.016}$ )

				0
Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	30	1.18
By Faston connectors	45	1.77	32	1.26
On printed circuit board	30	1.18	30	1.18


#### **Detail of Lug Recess**



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) Ø22.5 mm recommended (Ø22.3  $_0^{+0.4}$ ) / Ø0.89 in. recommended (Ø0.88 in.  $_0^{+0.016}$ )

# Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection


#### Panel Cut-outs (Viewed from Installer's Side)



**A:** 30 mm min. / 1.18 in. min. **B:** 40 mm min. / 1.57 in. min.


Printed Circuit Board Cut-outs (Viewed from Electrical Block Side)

Dimensions in mm



**A:** 30 mm min. **B:** 40 mm min.

Dimensions in in.



**A:** 1.18 in. min. **B:** 1.57 in. min.

#### General Tolerances of the Panel and Printed Circuit Board


The cumulative tolerance must not exceed 0.3 mm / 0.012 in.: T1 + T2 = 0.3 mm max.

#### **Installation Precautions**

- $_{\bullet}$  Minimum thickness of circuit board: 1.6 mm / 0.06 in.
- Cut-out diameter: 22.4 mm ± 0.1 / 0.88 in. ± 0.004
- Orientation of body/fixing collar ZB5AZ009: ± 2 30' (excluding cut-outs marked **a** and **b**).
- Tightening torque of screws ZBZ006: 0.6 N.m (5.3 lbf.in) max.
- Allow for one ZB5AZ079 fixing collar/pillar and its fixing screws:
  - $_{\circ}~$  every 90 mm / 3.54 in. horizontally (X), and 120 mm / 4.72 in. vertically (Y).
  - o with each selector switch head (ZB5AD•, ZB5AJ•, ZB5AG•).

The fixing centers marked  ${\bf a}$  and  ${\bf b}$  are diagonally opposed and must align with those marked  ${\bf 4}$  and  ${\bf 5}$ .

### **ZB5AW533**



- (1) Head ZB5AD•
- (2) Panel
- (2) Nut
- (4) Printed circuit board

#### Mounting of Adapter (Socket) ZBZ01•

- 1 2 elongated holes for ZBZ006 screw access
- 2 1 hole Ø 2.4 mm ± 0.05 / 0.09 in. ± 0.002 for centring adapter ZBZ01•
- 3 8 × Ø 1.2 mm / 0.05 in. holes
- 4 1 hole Ø 2.9 mm ± 0.05 / 0.11 in. ± 0.002, for aligning the printed circuit board (with cut-out marked a)
- 5 1 elongated hole for aligning the printed circuit board (with cut-out marked b)
- 6 4 holes Ø 2.4 mm / 0.09 in. for clipping in adapter ZBZ01•


Dimensions An + 18.1 relate to the Ø 2.4 mm  $\pm$  0.05 / 0.09 in.  $\pm$  0.002 holes for centring adapter ZBZ01•.

# **Product data sheet**


# **ZB5AW533**

**Technical Description** 


**Electrical Composition Corresponding to Codes M1 and M7** 



# **Electrical Composition Corresponding to Codes M2 and M8**



# **Electrical Composition Corresponding to Codes M6 and P2**



# Electrical Composition Corresponding to Codes M5, M10, MF1, MR1 and MF2



# Legend

Single contact



Double contact



Light block



Possible location

