Product data sheet

Specifications





Illuminated double headed push button head, Harmony XB5, plastic, 22mm, 1 green flush I + 1 pilot light + 1 red projecting O

ZB5AW7L3741

Product availability: Stock - Normally stocked in distribution facility

Price*: 49.50 USD

Main

Range Of Product	Harmony XB5	
Product Or Component Type	Head for illuminated double-headed push-button	
Product Compatibility	Integral LED	
Device Short Name	ZB5	
Bezel Material	Dark grey plastic	
Head Type	Standard	
Mounting Diameter	0.87 in (22 mm)	
Sale Per Indivisible Quantity	1	
Shape Of Signaling Unit Head	Rectangular	
Type Of Operator	spring return	
Operator Profile	1 flush - 1 projecting push-buttons - 1 central pilot light	
Operators Description	Green "I" - red "O"	

Complementary

Cad Overall Width	1.18 in (30 mm)
Cad Overall Height	1.97 in (50 mm)
Cad Overall Depth	1.38 in (35 mm)
Net Weight	0.05 lb(US) (0.023 kg)
Operator Profile	Green flush, I white) Red projecting, O white)
Mechanical Durability	1000000 cycles
Station Name	XALD 1 cut-out
Device Presentation	Basic sub-assemblies

Environment

Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Electrical Shock Protection Class	Class II IEC 60536

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ip Degree Of Protection	IP66	
	IP69	
	IP69K	
Nema Degree Of Protection	NEMA 13	
	NEMA 4X	
Resistance To High Pressure Washer	1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m	
Ik Degree Of Protection	IK05 conforming to IEC 50102	
Standards	EN/IEC 60947-5-4	
	JIS C8201-5-1	
	EN/IEC 60947-1	
	UL 508	
	CSA C22.2 No 14	
	EN/IEC 60947-5-1	
	JIS C8201-1	
Product Certifications	LROS (Lloyds register of shipping)	
	UL Listed	
	GL	
	CSA	
	DNV	
	BV	
Vibration Resistance	5 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27	
	50 gn 11 ms) half sine wave acceleration IEC 60068-2-27	

Ordering and shipping details

Category	US10CS222467
Discount Schedule	0CS2
Gtin	3389119043380
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.17 in (5.5 cm)
Package 1 Width	1.30 in (3.3 cm)
Package 1 Length	2.09 in (5.3 cm)
Package 1 Weight	0.92 oz (26.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	200
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	12.52 lb(US) (5.678 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information


Dimensions Drawings

Dimensions

Without Boot



With Boot ZBA710




Product data sheet


ZB5AW7L3741

Technical Description

Electrical Composition Corresponding to Codes M1 and M7



Electrical Composition Corresponding to Codes M2 and M8



Electrical Composition Corresponding to Codes M6 and P2



Electrical Composition Corresponding to Codes M5, M10, MF1, MR1 and MF2




Legend

Single contact



Double contact



Light block



Possible location

