



pushbutton head for harsh environment - green - with marking

ZB4BC38037

- ! Discontinued on: Dec 2, 2020
- ! End-of-service on: Dec 31, 2020

! Discontinued

Main

Range Of Product	Harmony XB4	
Product Or Component Type	Head for push-button	
Device Short Name	ZB4	
Bezel Material	Chromium plated metal	
Head Type	Standard	
Mounting Diameter	0.89 in (22.5 mm)	
Sale Per Indivisible Quantity	1	
Cap/Operator Or Lens Colour	Green	

Complementary

Cad Overall Width	1.46 in (37 mm)	
Cad Overall Height	0.73 in (18.5 mm)	
Cad Overall Depth	1.46 in (37 mm)	
Net Weight	0.08 lb(US) (0.036 kg)	
Electrical Shock Protection Class	Class I IEC 61140	
Shape Of Signaling Unit Head	Round	
Type Of Operator	spring return	
Operator Profile	Green flush, type H037 white)	
Operator Additional Information	Vertical mounting	
Mechanical Durability	10000000 cycles	
Vibration Resistance	5 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27	
Main Group	Harsh environment	
Group Of Product	Flush marked type H037	
Marking	Type H037	
Colour Of Marking	White	
Electrical Composition Code	C1 9 single front mounting C2 9 single and double front mounting C1 3 single front mounting	

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

C15 1 single front mounting





Ambient Air Temperature For Storage	-40185 °F (-4085 °C)	
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)	
Ip Degree Of Protection	IP66 IEC 60529 IP69K IP67 IP69	
Nema Degree Of Protection	NEMA 4 UL 508 NEMA 13 NEMA 12	
Resistance To High Pressure Washer	0.01 psi (90 Pa) 180 °F (82.5 °C)	
Ik Degree Of Protection	IK06 conforming to IEC 62262	
Standards	UL 508 CSA C22.2 IEC 60947-1 IEC 60947-5-1	
Product Certifications	CE UL CSA	

Ordering and shipping details

Category	22468-PUSHBUTTONS,22MM(METAL) NEW	
Discount Schedule	CS2	
Gtin	3606480444555	
Returnability	No	
Country Of Origin	FR	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.48 in (3.76 cm)	
Package 1 Width	1.46 in (3.7 cm)	
Package 1 Length	1.46 in (3.7 cm)	
Package 1 Weight	1.27 oz (36.0 g)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


②	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings


Dimensions



Mounting and Clearance


Installation on Flat Surface

Without Protective Guard



(1) Ø22.5 mm recommended (Ø22.3 $_0^{+0.4}$) / Ø0.89 in. recommended (Ø0.88 $_0^{+0.016}$)

With Protective Guard



(1) Ø22.5 mm recommended (Ø22.3 $_0^{+0.4}$) / Ø0.89 in. recommended (Ø0.88 $_0^{+0.016}$)

ZB4BC38037

Technical Description

Marking Type H037



Electrical Composition Corresponding to Code C1



Electrical Composition Corresponding to Code C2



ZB4BC38037

Electrical Composition Corresponding to Codes C9, C11, SF1 and SR1



Electrical Composition Corresponding to Code C15





1 N/C



1 N/O + N/C or 1 N/O + N/O or 1 N/C + N/C



ZB4BC38037

Eegend Single contact Double contact Light block Possible location