

Product data sheet

Specifications



orange light block for head Ø22
integral LED 110...120V screw
terminal for lugs

ZBVG59

⚠ Discontinued on: Dec 2, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

Main

Range Of Product	Harmony XB4 Harmony XB5
Product Or Component Type	Light block
Device Short Name	ZBV
Sale Per Indivisible Quantity	5
Connections - Terminals	Screw terminals for lug
Signalling Type	Steady
Light Source	Protected LED
Bulb Base	Integral LED
Light Block Supply	Direct
Light Source Colour	Orange
[Us] Rated Supply Voltage	110...120 V AC 50/60 Hz

Complementary

Net Weight	0.04 lb(US) (0.017 kg)
Current Consumption	14 mA
Service Life	100000 h at rated voltage and 25 °C
Surge Withstand	1 kV IEC 61000-4-5
Mounting Of Block	Front mounting
Electrical Composition Code	M1 M2 M3 M4 M5 M6 M10 MF1 P1 P2 PF1

Environment

Protective Treatment	TH
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-40...158 °F (-40...70 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP20 IEC 60529
Standards	UL 508 JIS C8201-5-1 EN/IEC 60947-5-5 EN/IEC 60947-5-4 EN/IEC 60947-1 EN/IEC 60947-5-1 CSA C22.2 No 14 JIS C8201-1
Resistance To Fast Transients	2 kV IEC 61000-4-4
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) IEC 61000-4-3
Resistance To Electrostatic Discharge	6 kV on contact (on metal parts) IEC 61000-4-2 8 kV in free air (in insulating parts) IEC 61000-4-2
Electromagnetic Emission	Class B IEC 55011
[Us] Rated Supply Voltage	110...120 V

Ordering and shipping details

Gtin	3389110177749
------	---------------

Contractual warranty

Warranty	18 months
----------	-----------