Specifications





Head for key selector switch, Harmony XB5, Harmony XALF, key switch selector head, plastic, black, 22mm, key 421E, 2 positions, stay put

ZB5AG212

Product availability: Stock - Normally stocked in distribution facility

Price\*: 90.00 USD

#### Main

Range Of Product	Harmony XB5 Harmony XALF			
Product Or Component Type	Head for key selector switch			
Device Short Name	ZB5			
Bezel Material	Dark grey plastic			
Mounting Diameter	0.87 in (22 mm)			
Head Type	Standard			
Sale Per Indivisible Quantity	1			
Shape Of Signaling Unit Head	Round			
Type Of Operator	stay put			
Operator Profile	Black key switch			
Operator Position Information	2 positions 90°			
Type Of Keylock	Key 421E			
Key Withdrawal Position	Left			

# Complementary

•					
Cad Overall Width	1.14 in (29 mm)				
Cad Overall Height	1.14 in (29 mm)				
Cad Overall Depth	2.83 in (72 mm)				
Net Weight	0.13 lb(US) (0.057 kg)				
Mechanical Durability	1000000 cycles				
Station Name	XALD 15 cut-outs XALK 25 cut-outs				
Electrical Composition Code	C4 6 single and double front mounting C5 5 single front mounting C6 5 single and double front mounting C7 4 single front mounting C8 4 single and double front mounting C11 3 single front mounting C3 6 single front mounting SF1 3 single front mounting				

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

SR1 3 single rear mounting C15 1 single front mounting

Device Presentation Basic element

# **Environment**

Protective Treatment	тн				
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)				
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)				
Overvoltage Category	Class II IEC 60536				
Ip Degree Of Protection	IP66 IEC 60529 IP67 IP69 IP69K				
Nema Degree Of Protection	NEMA 13 NEMA 4X				
Resistance To High Pressure Washer	1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m				
Ik Degree Of Protection	IK06 conforming to IEC 50102				
Standards	IEC 60947-1 IEC 60947-5-4 JIS C8201-5-1 IEC 60947-5-1 CSA C22.2 No 14 UL 508 JIS C8201-1				
Product Certifications	CSA DNV LROS (Lloyds register of shipping) GL BV UL Listed				
Vibration Resistance	5 gn 2500 Hz)IEC 60068-2-6				
Shock Resistance	tance 30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27				

# Ordering and shipping details

Category	US10CS222467			
Discount Schedule	0CS2			
Gtin	3389110135206			
Returnability	Yes			
Country Of Origin	FR			

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	2.17 in (5.5 cm)
Package 1 Length	3.58 in (9.1 cm)
Package 1 Weight	2.36 oz (67.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	3.43 in (8.7 cm)

Package 2 Width	1.34 in (3.4 cm)		
Package 2 Length	10.24 in (26.0 cm)		
Package 2 Weight	11.82 oz (335.0 g)		
Unit Type Of Package 3	S02		
Number Of Units In Package 3	50		
Package 3 Height	5.91 in (15.0 cm)		
Package 3 Width	11.81 in (30.0 cm)		
Package 3 Length	15.75 in (40.0 cm)		
Package 3 Weight	8.17 lb(US) (3.706 kg)		

# **Contractual warranty**

Warranty 18 months

# Sustainability Green Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes


## **Certifications & Standards**

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
China Rohs Regulation	China RoHS declaration				
<b>Environmental Disclosure</b>	Product Environmental Profile				
Circularity Profile	End of Life Information				
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov				

# **ZB5AG212**

# **Dimensions Drawings**


## **Dimensions**



#### Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


#### Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) Ø22.5 mm recommended (Ø22.3  $_0^{+0.4}$ ) / Ø0.89 in. recommended (Ø0.88 in.  $_0^{+0.016}$ )

				0
Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	30	1.18
By Faston connectors	45	1.77	32	1.26
On printed circuit board	30	1.18	30	1.18


#### **Detail of Lug Recess**



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) Ø22.5 mm recommended (Ø22.3  $_0^{+0.4}$ ) / Ø0.89 in. recommended (Ø0.88 in.  $_0^{+0.016}$ )

### Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection


#### Panel Cut-outs (Viewed from Installer's Side)




**A:** 30 mm min. / 1.18 in. min. **B:** 40 mm min. / 1.57 in. min.

Printed Circuit Board Cut-outs (Viewed from Electrical Block Side)

Dimensions in mm



A: 30 mm min. B: 40 mm min. Dimensions in in.



**A:** 1.18 in. min. **B:** 1.57 in. min.


#### General Tolerances of the Panel and Printed Circuit Board

The cumulative tolerance must not exceed 0.3 mm / 0.012 in.: T1 + T2 = 0.3 mm max.

#### **Installation Precautions**

- $_{\bullet}$  Minimum thickness of circuit board: 1.6 mm / 0.06 in.
- Cut-out diameter: 22.4 mm ± 0.1 / 0.88 in. ± 0.004
- Orientation of body/fixing collar ZB5AZ009: ± 2 30' (excluding cut-outs marked **a** and **b**).
- Tightening torque of screws ZBZ006: 0.6 N.m (5.3 lbf.in) max.
- Allow for one ZB5AZ079 fixing collar/pillar and its fixing screws:
  - $_{\circ}~$  every 90 mm / 3.54 in. horizontally (X), and 120 mm / 4.72 in. vertically (Y).
  - o with each selector switch head (ZB5AD•, ZB5AJ•, ZB5AG•).

The fixing centers marked  ${\bf a}$  and  ${\bf b}$  are diagonally opposed and must align with those marked  ${\bf 4}$  and  ${\bf 5}$ .



- (1) Head ZB5AD•
- (2) Panel
- (2) Nut

10

(4) Printed circuit board

#### Mounting of Adapter (Socket) ZBZ01•

- 1 2 elongated holes for ZBZ006 screw access
- 2 1 hole Ø 2.4 mm ± 0.05 / 0.09 in. ± 0.002 for centring adapter ZBZ01•
- 3 8 × Ø 1.2 mm / 0.05 in. holes
- 4 1 hole Ø 2.9 mm ± 0.05 / 0.11 in. ± 0.002, for aligning the printed circuit board (with cut-out marked a)
- 5 1 elongated hole for aligning the printed circuit board (with cut-out marked b)
- 6 4 holes Ø 2.4 mm / 0.09 in. for clipping in adapter ZBZ01•

Dimensions An + 18.1 relate to the Ø 2.4 mm  $\pm$  0.05 / 0.09 in.  $\pm$  0.002 holes for centring adapter ZBZ01•.


# **ZB5AG212**


**Technical Description** 

**Electrical Composition Corresponding to Code C4** 





11





13







# **ZB5AG212**

**Electrical Composition Corresponding to Codes C9, C11, SF1 and SR1** 




## Legend

Single contact



Double contact



Light block



Possible location



## Sequence of Contacts Fitted to 2-position Selector Switch Body

#### Position 315°



Push	Position	Тор				
		Bottom				
	Location		Left	Centre	Right	
	State		0	0	0	
Contacts	N/O		open	open	open	
	N/C		closed	closed	closed	

#### Position 45°



Push		Тор			
	Position	Bottom			
	Location		Left	Centre	Right
	State		1	1	1
Contacts	N/O		closed	closed	closed
	N/C		open	open	open