Product data sheet

Specification





Head for key selector switch, Harmony XB5, flush mounted blue 2 pos stay put

ZB5FD206

Product availability: Stock - Normally stocked in distribution

Price*: 24.30 USD

Main

| Range Of Product | Harmony XB5 | | | |
|-------------------------------|------------------------------|--|--|--|
| Product Or Component Type | Head for key selector switch | | | |
| Device Short Name | ZB5 | | | |
| Bezel Material | Dark grey plastic | | | |
| Mounting Diameter | 1.20 in (30.5 mm) | | | |
| Head Type | Built-in-flush | | | |
| Sale Per Indivisible Quantity | 1 | | | |
| Shape Of Signaling Unit Head | Round | | | |
| Type Of Operator | stay put | | | |
| Operator Profile | Blue standard handle | | | |
| Operator Position Information | 2 positions 90° | | | |

Complementary

| Cad Overall Width | 1.46 in (37 mm) | | | | |
|-----------------------------|--|--|--|--|--|
| Cad Overall Height | 1.46 in (37 mm) | | | | |
| Cad Overall Depth | 1.81 in (46 mm) | | | | |
| Net Weight | 0.07 lb(US) (0.031 kg) | | | | |
| Mechanical Durability | 1000000 cycles | | | | |
| Electrical Composition Code | C3 6 single front mounting C4 6 single and double front mounting C5 5 single front mounting C6 5 single and double front mounting C7 4 single front mounting C8 4 single and double front mounting C11 3 single front mounting C15 1 single front mounting SF1 3 single front mounting | | | | |

Environment

| Protective Treatment | тн |
|---------------------------------------|----------------------|
| Ambient Air Temperature For Storage | -40158 °F (-4070 °C) |
| Ambient Air Temperature For Operation | -40158 °F (-4070 °C) |
| Overvoltage Category | Class II IFC 60536 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Ip Degree Of Protection | IP66 IEC 60529 IP67 IEC 60529 IP69K | | | |
|------------------------------------|---|--|--|--|
| | IP69 | | | |
| Nema Degree Of Protection | NEMA 13 NEMA 4X | | | |
| Resistance To High Pressure Washer | 1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m | | | |
| Ik Degree Of Protection | IK03 conforming to IEC 50102 | | | |
| Standards | JIS C8201-5-1 EN/IEC 60947-5-4 EN/IEC 60947-1 UL 508 CSA C22.2 No 14 EN/IEC 60947-5-1 JIS C8201-1 | | | |
| Product Certifications | LROS (Lloyds register of shipping) DNV CSA BV UL Listed GL | | | |
| Vibration Resistance | 5 gn 2500 Hz)IEC 60068-2-6 | | | |
| Shock Resistance | 30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27 | | | |

Ordering and shipping details

| Category | US10CS222467 | | |
|-------------------|---------------|--|--|
| Discount Schedule | 0CS2 | | |
| Gtin | 3606481339805 | | |
| Returnability | No | | |
| Country Of Origin | FR | | |

Packing Units

| Unit Type Of Package 1 | PCE | | |
|------------------------------|-----------------------|--|--|
| Number Of Units In Package 1 | 1 | | |
| Package 1 Height | 2.10 in (5.33 cm) | | |
| Package 1 Width | 1.70 in (4.32 cm) | | |
| Package 1 Length | 2.20 in (5.59 cm) | | |
| Package 1 Weight | 0.07 lb(US) (0.03 kg) | | |



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


| ⊘ | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| ⊘ | Toxic Heavy Metal Free | |
| ⊘ | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Dimensions Drawings

Dimensions




e: Clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

ZB5FD206

Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors



(1) Diameter on finished panel or support


(2) Ø30.75 mm recommended (Ø30.5 $_0^{+0.5}$) / Ø1.21 in. recommended (Ø1.20 in. $_0^{+0.0196}$)


| 0 | | | | 0 |
|---|---------|----------|---------|----------|
| Connections | a in mm | a in in. | b in mm | b in in. |
| By screw clamp terminals or plug-in connector | 40 | 1.57 | 40 | 1.57 |
| By Faston connectors | 45 | 1.77 | 40 | 1.57 |


Technical Description














Electrical Composition Corresponding to Codes C9, C11, SF1 and SR1



1 N/O



1 N/C



1 N/O + N/C or 1 N/O + N/O or 1 N/C + N/C




Legend

Single contact



Double contact



Light block



Possible location



Sequence of Contacts Fitted to 2-position Selector Switch Body

Position 315°



| Push | Position | Тор | | | | |
|----------|----------|--------|--------|--------|--------|--|
| | | Bottom | | | | |
| | Location | | Left | Centre | Right | |
| | State | | 0 | 0 | 0 | |
| Contacts | N/O | | open | open | open | |
| | N/C | | closed | closed | closed | |

Position 45°



| | | Тор | | | |
|----------|----------|--------|--------|--------|--------|
| Push | Position | Bottom | | | |
| | Location | | Left | Centre | Right |
| | State | | 1 | 1 | 1 |
| Contacts | N/O | | closed | closed | closed |
| Contacts | N/C | | open | open | open |