# Product data sheet

Specification





Head for illuminated selector switch, Harmony XB5, plastic, orange handle, universal LED, 2 positions, stay put

ZB5FK1253

Product availability: Non-Stock - Not normally stocked in distribution facility

Important message: A change in appearance may be noted on the product but does not affect its use in terms of function and safety. This makes it compatible with our Universal LED blocks

Price\*: 35.30 USD

#### Main

Range Of Product	Harmony XB5			
Product Or Component Type	Head for illuminated selector switch			
Product Compatibility	Universal LED			
Device Short Name	ZB5			
Bezel Material	Dark grey plastic			
Mounting Diameter	1.20 in (30.5 mm)			
Head Type	Built-in-flush			
Sale Per Indivisible Quantity	1			
Shape Of Signaling Unit Head	Round			
Type Of Operator	stay put			
Operator Profile	Orange standard handle			
Operator Position Information	2 positions 90°			

## Complementary

Cad Overall Width	1.46 in (37 mm)
Cad Overall Height	1.46 in (37 mm)
Cad Overall Depth	1.81 in (46 mm)
Net Weight	0.07 lb(US) (0.03 kg)
Mechanical Durability	1000000 cycles
Electrical Composition Code	M3 4 single front mounting integral LED M6 2 single front mounting integral LED and transformer M10 2 single front mounting integral LED MF1 2 single front mounting integral LED M4 4 single and double front mounting integral LED
Device Presentation	Basic element

#### **Environment**

Protective Treatment	тн
Ambient Air Temperature For	-40158 °F (-4070 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Overvoltage Category	Class II IEC 60536
Ip Degree Of Protection	IP66 IEC 60529 IP67 IP69 IP69K
Nema Degree Of Protection	NEMA 13 NEMA 4X
Resistance To High Pressure Washer	1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m
Ik Degree Of Protection	IK03 conforming to IEC 50102
Standards	UL 508 EN/IEC 60947-5-4 CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-5-5 JIS C8201-5-1 EN/IEC 60947-1 JIS C8201-1
Product Certifications	CSA DNV UL Listed LROS (Lloyds register of shipping) GL BV
Vibration Resistance	5 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27

# Ordering and shipping details

Category	US10CS222467				
Discount Schedule	0CS2				
Gtin	3606481339515				
Returnability	No				
Country Of Origin	FR				

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.15 in (5.45 cm)
Package 1 Width	1.69 in (4.3 cm)
Package 1 Length	2.05 in (5.2 cm)
Package 1 Weight	0.78 oz (22.0 g)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance


<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

## **Dimensions Drawings**

#### **Dimensions**



e: Clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.


# **Product data sheet**

#### **ZB5FK1253**

## Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

#### Connection by Screw Clamp Terminals or Plug-in Connectors



(1) Diameter on finished panel or support

(2) Ø30.75 mm recommended (Ø30.5  $_0^{+0.5}$ ) / Ø1.21 in. recommended (Ø1.20 in.  $_0^{+0.0196}$ )


0				U
Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	40	1.57
By Faston connectors	45	1.77	40	1.57

# **Product data sheet**


# **ZB5FK1253**

**Technical Description** 

**Electrical Composition Corresponding to Code M3** 



## **Electrical Composition Corresponding to Code M4**



## **Electrical Composition Corresponding to Codes M6 and P2**



## Electrical Composition Corresponding to Codes M5, M10, MF1, MR1 and MF2



1	.ea	e	n	d
_	.cy	C		·

Single contact



Double contact



Light block



Possible location



## Sequence of Contacts Fitted to 2-position Selector Switch Body

#### Position 315°



	Position	Тор		
Push		Bottom		
	Location		Left	Right
	State		0	0
Contonto	N/O		open	open
Contacts	N/C		closed	closed

#### Position 45°



		Тор		
Push	Position	Bottom		
	Location		Left	Right
	State		1	1
	N/O		closed	closed
Contacts	N/C		open	open