

ZCKSD39

limit switch body ZCKS - 2NC+1NO - snap action
- Pg13.5

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 46.64 USD



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch body
Device short name	ZCKS
Body type	Fixed
Product compatibility	XCKS
Associated head	ZCKD019 ZCKD41 ZCKD01 ZCKD81 ZCKD34 ZCKD59 ZCKD02 ZCKD39 ZCKD05 ZCKD33 ZCKD31 ZCKD08 ZCKD49 ZCKD55 ZCKD91 ZCKD54 ZCKD029 ZCKD06
Body material	Plastic
Cable entry	1 entry tapped for Pg 13.5 cable gland
Number of poles	3
Contacts type and composition	2 NC + 1 NO
Contact operation	Snap action
Number of steps	1 1 position
Contacts material	Silver plated contacts

Complementary

Local display	Without
Electrical connection	Screw-clamp terminals, clamping capacity: 1 x 0.34...2 x 0.75 mm ²
Positive opening	With
Minimum actuation speed	0.01 m/min
[Ie] rated operational current	1.5 A at 240 V, AC-15, B300 conforming to EN/IEC 60947-5-1 appendix A 0.1 A at 250 V, DC-13, R300 conforming to EN/IEC 60947-5-1 appendix A
[Ithe] conventional enclosed thermal current	6 A
[Ui] rated insulation voltage	300 V conforming to CSA C22.2 No 14 contact block 300 V conforming to UL 508 contact block 400 V degree of pollution 3 conforming to IEC 60947-1 contact block
Resistance across terminals	0.25 mOhm conforming to IEC 60255-7 category 3
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60664 4 kV conforming to IEC 60947-1
Short-circuit protection	6 A by gG cartridge fuse
Electrical durability	5000000 cycles, DC-13 120 V, 1 W, operating rate: < 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 5000000 cycles, DC-13 24 V, 3 W, operating rate: < 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 5000000 cycles, DC-13 48 V, 2 W, operating rate: < 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C
Width	1.57 in (40 mm)
Height	2.87 in (73 mm)
Depth	1.42 in (36 mm)
Product weight	0.18 lb(US) (0.08 kg)
Terminals description ISO n°1	(21-22)NC (31-32)NC (13-14)NO

Environment

IP degree of protection	IP65
IK degree of protection	IK03
Ambient air temperature for operation	-13...158 °F (-25...70 °C) standard environment
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	003389110904345
Nbr. of units in pkg.	1
Package weight(Lbs)	0.16
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1014 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:

----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------