

Product data sheet

Specifications



time delay relay 9 functions - 1 s..
100 h - 24..240 V AC - 1 OC

RE11RXXMU

⚠ Discontinued on: Mar 31, 2020

⚠ Discontinued

Main

Range Of Product	Zelio Time
Product Or Component Type	Modular timing relay
Discrete Output Type	Relay
Component Name	RE11R
Time Delay Type	P N T W Pt Ad Ah Tt O
Time Delay Range	0.1...1 s 6...60 min 10...100 h 1...10 h 6...60 s 1...10 min 1...10 s
[Us] Rated Supply Voltage	24...240 V AC 50/60 Hz 24 V DC
Nominal Output Current	8 A

Complementary

Contacts Material	AgNi (cadmium free)
Width Pitch Dimension	0.69 in (17.5 mm)
Control Type	Selector switch front panel
Voltage Range	0.85...1.1 Us
Connections - Terminals	Screw terminals, 2 x 1.5 mm² without cable end Screw terminals, 2 x 2.5 mm² + 1 x 4 mm² with cable end
Housing Material	Self-extinguishing
Repeat Accuracy	+/- 0.5 % IEC 61812-1
Temperature Drift	+/- 0.05 %/°C
Voltage Drift	+/- 0.2 %/V
Setting Accuracy Of Time Delay	+/- 10 % of full scale 25 °C IEC 61812-1
Minimum Pulse Duration	100 ms with load in parallel 30 ms

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum Reset Time	100 ms on de-energisation
On-Load Factor	100 %
Maximum Power Consumption	32 VA 240 V
Maximum Power Consumption	0.6 W 24 V 1.5 W 240 V
Minimum Switching Current	10 mA
Maximum Switching Current	8 A
Maximum Switching Voltage	150 V DC 250 V AC
Breaking Capacity	2000 VA
Breaking Capacity	80 W
Electrical Durability	100000 cycles 8 A, 250 V resistive
Mechanical Durability	5000000 cycles
[Uimp] Rated Impulse Withstand Voltage	5 kV 1.2...50 µs IEC 60664-1 5 kV 1.2...50 µs IEC 61812-1
Marking	CE
Creepage Distance	4 kV/3 IEC 60664-1
Surge Withstand	1 kV differential mode IEC 61000-4-5 level 3 2 kV common mode IEC 61000-4-5 level 3
Mounting Support	35 mm symmetrical mounting rail conforming to EN 50022
Local Signalling	for flashing: timing in progress LED indicator (green) for on steady: relay energised, no timing in progress LED indicator (green) for pulsing: relay energised, no timing in progress (except functions Di-D) LED indicator (green)
Net Weight	0.13 lb(US) (0.06 kg)

Environment

Immunity To Microbreaks	10 ms
Dielectric Strength	2.5 kV 1 mA/1 minute 50 Hz IEC 61812-1
Standards	IEC 60669-2-3 73/23/EEC IEC 61812-1 EN 50082-1/2 93/68/EEC 89/336/EEC EN 50081-1/2
Product Certifications	GL CSA cULus
Ambient Air Temperature For Storage	-22...140 °F (-30...60 °C)
Ambient Air Temperature For Operation	-4...140 °F (-20...60 °C)
Ip Degree Of Protection	IP20 IEC 60529 terminal block) IP40 IEC 60529 housing) IP50 IEC 60529 front panel)
Vibration Resistance	0.35 mm 10...55 Hz)(IEC 60068-2-6
Relative Humidity	93 % without condensation IEC 60068-2-3
Resistance To Electrostatic Discharge	6 kV in contact IEC 61000-4-2 level 3 8 kV in air IEC 61000-4-2 level 3
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) 80 MHz to 1 GHz ENV 50140/204 level 3 9.14 V/m (10 V/m) 80 MHz to 1 GHz IEC 61000-4-3 level 3

Resistance To Fast Transients	1 kV IEC 61000-4-4 level 3 capacitive connecting clip) 2 kV IEC 61000-4-4 level 3 direct)
Immunity To Radioelectric Fields	10 V 0.15...80 MHz)ENV 50141 (IEC 61000-4-6)
Immunity To Voltage Dips	30 % / 10 ms IEC 61000-4-11 60 % / 100 ms IEC 61000-4-11 95 % / 5 s IEC 61000-4-11
Disturbance Radiated/Conducted	Class B EN 55022 (EN 55011 group 1)

Ordering and shipping details


Category	22370-RE, RM MISC TIMERS & COUNTERS
Discount Schedule	CP2
Gtin	00785901570745
Returnability	No
Country Of Origin	FR

Contractual warranty

Warranty	18 months
----------	-----------


Dimensions Drawings

Width 17.5 mm




Connections and Schema

Internal Wiring Diagram



Wiring Diagram



1) Contact Y1:

- Control for functions B, C, Ac, Bw, Ad, Ah, N, O, W, T, Tt.
- Partial stop for functions At, Ht and Pt.
- Function D if Di selected.
- Not used for functions A, H and P.


Technical Description

Function Ad : Pulse Delayed Relay with Control Signal

Description

After power-up, pulsing or maintaining of control contact C starts the timing T.
At the end of this timing period T, the output R closes.
The output R will be reset the next time control contact C is pulsed or maintained.

Function: 1 Output



Function Ah : Pulse Delayed Relay (Single Cycle) with Control Signal

Description

After power-up, pulsing or maintaining of control contact C starts the timing T. A single cycle then starts with 2 timing periods T of equal duration (start with output in rest position). Output R closes at the end of the first timing period T and reverts to its initial position at the end of the second timing period T. Control contact C must be reset in order to re-start the single flashing cycle.

Function: 1 Output



Function N : Retriggerable Interval Relay with Control Signal On

Description

After power-up and an initial control pulse C, the output R closes.
If the interval between two control pulses C is greater than the set timing period T, timing elapses normally and the output R closes at the end of the timing period. If the interval is not greater than the set timing period, the output R remains closed until this condition is met.

Function: 1 Output




Function O : Retriggerable Interval Delayed Relay with Control Signal On

Description

An initial timing period T begins on energisation. At the end of this timing period, the output R closes.
As soon as there is a control pulse C, the output R reverts to its initial state until the interval between two control pulses is less than the value of the set timing period T. Otherwise, the output R closes at the end of the timing period T.

Function: 1 Output



Function P : Pulse Delayed Relay with Fixed Pulse Length

Description

The timing period T begins on energisation.
At the end of this period, the output R closes for a fixed time P.

Function: 1 Output




P = 500 ms

Function Pt : Pulse Delayed Relay (Summation and Fixed Pulse Length) with Control Signal Off

Description

On energisation, timing period T starts (it can be interrupted by operating the Gate control contact G).
At the end of this period, the output R closes for a fixed time P.

Function: 1 Output



$T = t1 + t2 + \dots$
 $P = 500 \text{ ms}$

Function T : Bistable Relay with Control Signal On

Description

After power-up, pulsing or maintaining of control contact C switches the output on.
A second pulse on the control contact C switches the output R off.

Function: 1 Output



Function Tt : Retriggerable Bistable Relay with Control Signal On

Description

After power-up, pulsing or maintaining of control contact C switches output R on and starts timing T. The output switches off at the end of the timing period T or following a second pulse on the control contact C.

Function: 1 Output



Function W : Interval Relay with Control Signal Off


Description

After power-up and opening of the control contact, the output(s) close(s) for a timing period T.
At the end of this timing period the output(s) revert(s) to its/their initial state.
The second output can be either timed or instantaneous.

Function: 1 Output







Function: 2 Outputs



2 timed outputs (R1/R2) or 1 timed output (R1) and 1 instantaneous output (R2 inst.).

Legend

-  Relay de-energised
-  Relay energised
-  Output open
-  Output closed

C	Control contact
G	Gate
R	Relay or solid state output
R1/R2	2 timed outputs
R2 inst.	The second output is instantaneous if the right position is selected
T	Timing period
Ta -	Adjustable On-delay
Tr -	Adjustable Off-delay
U	Supply