Product data sheet

Specification





logic controller, Modicon M221, 40 IO, transistor, PNP

TM221C40T

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 369.00 USD

Main

Range Of Product	Modicon M221	
Product Or Component Type	Logic controller	
[Us] Rated Supply Voltage	24 V DC	
Discrete Input Number	24, discrete input 4 fast input IEC 61131-2 Type 1	
Analogue Input Number	2 010 V	
Discrete Output Type	Transistor	
Discrete Output Number	16 transistor 2 fast output	
Discrete Output Voltage	24 V DC	
Discrete Output Current	0.5 A	

Complementary

Discrete I/O Number	40
Maximum Number Of I/O Expansion Module	7 (local I/O-Architecture) 14 (remote I/O-Architecture)
Supply Voltage Limits	20.428.8 V
Inrush Current	35 A
Maximum Power Consumption In W	4.1 W 24 V without I/O expansion module) 16 W 24 V with max number of I/O expansion module)
Power Supply Output Current	0.52 A 5 V expansion bus 0.3 A 24 V expansion bus
Discrete Input Logic	Sink or source (positive/negative)
Discrete Input Voltage	24 V
Discrete Input Voltage Type	DC
Analogue Input Resolution	10 bits
Lsb Value	10 mV
Conversion Time	1 ms per channel + 1 controller cycle time analog input
Permitted Overload On Inputs	+/- 30 V DC 5 min maximum)analog input +/- 13 V DC permanent)analog input
Voltage State 1 Guaranteed	>= 15 V input
Voltage State 0 Guaranteed	<= 5 V input
Discrete Input Current	7 mA discrete input 5 mA fast input

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Input Impedance	3.4 kOhm discrete input	
	100 kOhm analog input 4.9 kOhm fast input	
	·	
Response Time	35 μs turn-off, I2I5 input 5 μs turn-on, I0, I1, I6, I7 fast input	
	35 µs turn-on, other terminals input	
	5 µs turn-off, I0, I1, I6, I7 fast input	
	100 µs turn-off, other terminals input	
	5 μs turn-on, turn-off, Q0Q1 output 50 μs turn-on, turn-off, Q2Q3 output	
	300 µs turn-on, turn-off, other terminals output	
Configurable Filtering Time	0 ms input	
	3 ms input	
	12 ms input	
Discrete Output Logic	Positive logic (source)	
Maximum Current Per Output Common	4 A	
Output Frequency (Sync To	100 kHz fast output (PWM/PLS mode) Q0Q1	
Mains)	5 kHz output Q2Q3	
	0.1 kHz output Q4Q15	
Absolute Accuracy Error	+/- 1 % of full scale analog input	
Maximum Leakage Current	0.1 mA transistor output	
Maximum Voltage Drop	<1 V	
Mechanical Durability	20000000 cycles transistor output	
Maximum Tungsten Load	<12 W output and fast output	
Protection Type	Overload and short-circuit protection 1 A	
Reset Time	1 s automatic reset	
Memory Capacity	256 kB user application and data RAM 10000 instructions 256 kB internal variables RAM	
Data Backed Up	256 kB built-in flash memory backup of application and data	
Data Storage Equipment	2 GB SD card optional)	
Battery Type	BR2032 or CR2032X lithium non-rechargeable	
Backup Time	1 year 77 °F (25 °C) by interruption of power supply)	
Execution Time For 1 Kinstruction	0.3 ms event and periodic task	
Execution Time Per Instruction	0.2 μs Boolean	
Exct Time For Event Task	60 μs response time	
Maximum Size Of Object Areas	255 %TM timers	
	512 %M memory bits	
	255 %C counters 512 %KW constant words	
	8000 %MW memory words	
Realtime Clock	With	
Clock Drift	<= 30 s/month 77 °F (25 °C)	
Regulation Loop	Adjustable PID regulator up to 14 simultaneous loops	
Positioning Functions	PTO 2 pulse/direction 100 kHz) PTO 1 CW/CCW 100 kHz)	
Function Available	Frequency generator	
	PWM PLS	
Counting Input Number	4 fast input (HSC mode) 100 kHz 32 bits	
Counter Function	Pulse/direction Single phase A/B	

Integrated Connection Type	LICE and mini P. LICE 2.0	
Integrated Connection Type	USB port mini B USB 2.0 Non isolated serial link serial 1 RJ45 RS485	
	Non isolated serial link serial 2 RJ45 RS232/RS485	
Supply	Serial)serial link supply 5 V, <200 mA	
Transmission Rate	1.2115.2 kbit/s (115.2 kbit/s by default) 49.21 ft (15 m) RS485	
	1.2115.2 kbit/s (115.2 kbit/s by default) 9.84 ft (3 m) RS232 480 Mbit/s USB	
Communication Port Protocol	USB port USB - SoMachine-Network Non isolated serial link Modbus master/slave - RTU/ASCII or SoMachine-Network	
Local Signalling	for PWR 1 LED (green)	
	for RUN 1 LED (green) for module error (ERR) 1 LED (red)	
	for SD card access (SD) 1 LED (green)	
	for BAT 1 LED (red)	
	for SL1 1 LED (green)	
	for SL2 1 LED (green) for I/O state 1 LED per channel (green)	
Electrical Connection	removable screw terminal block for inputs	
	removable screw terminal block for outputs	
	terminal block, 3 for connecting the 24 V DC power supply	
	connector, 4 for analogue inputs Mini B USB 2.0 connector for a programming terminal	
Maximum Cable Distance	Shielded cable <32.81 ft (10 m) fast input	
Between Devices	Unshielded cable <98.43 ft (30 m) output	
	Unshielded cable <98.43 ft (30 m) digital input	
	Unshielded cable <3.28 ft (1 m) analog input Shielded cable <9.84 ft (3 m) fast output	
Insulation	Between input and internal logic 500 V AC	
	Between fast input and internal logic 500 V AC	
	Non-insulated between inputs Between output and internal logic 500 V AC	
	Non-insulated between analogue input and internal logic	
	Non-insulated between analogue inputs	
Marking	CE	
Mounting Support	Top hat type TH35-15 rail IEC 60715	
	Top hat type TH35-7.5 rail IEC 60715 plate or panel with fixing kit	
Height	3.54 in (90 mm)	
Depth	2.76 in (70 mm)	
Width	6.30 in (160 mm)	
Net Weight	1.01 lb(US) (0.456 kg)	
Environment		
Standards	IEC 61131-2	
	UL 508 CAN/CSA C22.2 No. 213	
	IACS E10	
	ANSI/ISA 12-12-01	
Product Certifications	DNV-GL	
	ABS EAC	
	CULus	
	RCM	
	LR	
	CE UKCA	
	cULus HazLoc	
Environmental Characteristic	Ordinary and hazardous location	
Resistance To Electrostatic Discharge	8 kV in air IEC 61000-4-2	
Districting	4 kV on contact IEC 61000-4-2	

Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) 80 MHz1 GHz IEC 61000-4-3 2.74 V/m (3 V/m) 1.4 GHz2 GHz IEC 61000-4-3
	0.91 V/m (1 V/m) 22.7 GHz IEC 61000-4-3
Resistance To Magnetic Fields	98.43 A/m (30 A/m) 50/60 Hz IEC 61000-4-8
Resistance To Fast Transients	2 kV IEC 61000-4-4 power lines)
	2 kV IEC 61000-4-4 relay output)
	1 kV IEC 61000-4-4 I/O)
	1 kV IEC 61000-4-4 Ethernet line)
	1 kV IEC 61000-4-4 serial link)
Surge Withstand	2 kV power lines (AC) common mode IEC 61000-4-5
	2 kV relay output common mode IEC 61000-4-5
	1 kV I/O common mode IEC 61000-4-5
	1 kV shielded cable common mode IEC 61000-4-5
	0.5 kV power lines (DC) differential mode IEC 61000-4-5
	1 kV power lines (AC) differential mode IEC 61000-4-5
	1 kV relay output differential mode IEC 61000-4-5
	0.5 kV power lines (DC) common mode IEC 61000-4-5
Resistance To Conducted	10 V 0.1580 MHz IEC 61000-4-6
Disturbances	3 V 0.180 MHz Marine specification (LR, ABS, DNV, GL)
	10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) Marine
	specification (LR, ABS, DNV, GL)
Electromagnetic Emission	Conducted emissions 79 dBµV/m QP/66 dBµV/m AV power lines (AC))0.150.5 MHz IEC 55011
	Conducted emissions 73 dBµV/m QP/60 dBµV/m AV power lines (AC))0.5300 MHz
	IEC 55011
	Conducted emissions 12069 dBµV/m QP power lines)10150 kHz IEC 55011
	Conducted emissions 63 dBµV/m QP power lines)1.530 MHz IEC 55011
	Radiated emissions 40 dBµV/m QP class A 10 m)30230 MHz IEC 55011
	Conducted emissions 7963 dBµV/m QP power lines)1501500 kHz IEC 55011
	Radiated emissions 47 dBµV/m QP class A 10 m)2001000 MHz IEC 55011
Immunity To Microbreaks	10 ms
Ambient Air Temperature For	14131 °F (-1055 °C) horizontal installation)
Operation	1495 °F (-1035 °C) vertical installation)
Ambient Air Temperature For Storage	-13158 °F (-2570 °C)
Relative Humidity	1095 %, without condensation in operation)
	1095 %, without condensation in operation)
Ip Degree Of Protection	IP20 with protective cover in place
Pollution Degree	<= 2
Operating Altitude	06561.68 ft (02000 m)
Storage Altitude	0.009842.52 ft (03000 m)
Vibration Resistance	3.5 mm 58.4 Hz symmetrical rail
	3.5 mm 58.4 Hz panel mounting
	1 gn 8.4150 Hz symmetrical rail
	1 gn 8.4150 Hz panel mounting
Shock Resistance	147 m/s² 11 ms

Ordering and shipping details

Category	US10MSX22533
Discount Schedule	OMSX
Gtin	3606480648748
Returnability	No
Country Of Origin	CN

Packing Units

Unit Type Of Package 1 PCE

Number Of Units In Package 1	1
Package 1 Height	4.40 in (11.172 cm)
Package 1 Width	5.56 in (14.117 cm)
Package 1 Length	8.30 in (21.084 cm)
Package 1 Weight	26.46 oz (750.0 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	12
Package 2 Height	11.50 in (29.2 cm)
Package 2 Width	15.59 in (39.6 cm)
Package 2 Length	22.36 in (56.8 cm)
Package 2 Weight	22.27 lb(US) (10.101 kg)
Unit Type Of Package 3	P12
Number Of Units In Package 3	144
Package 3 Height	41.34 in (105.0 cm)
Package 3 Width	47.24 in (120.0 cm)
Package 3 Length	31.50 in (80.0 cm)
Package 3 Weight	297.62 lb(US) (135 kg)

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
②	Rohs Exemption Information	Yes
	Pvc Free	

Certifications & Standards


Reach Regulation	Pro-active compliance (Product out of EU RoHS legal scope)	
Eu Rohs Directive		
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	


Product data sheet

TM221C40T

Dimensions Drawings


Dimensions






Mounting and Clearance

Mounting on a Rail





Direct Mounting on a Panel Surface



(1) Install a mounting strip


Mounting Hole Layout






Mounting

Correct Mounting Position




Acceptable Mounting Position




Incorrect Mounting Position









Clearance





Connections and Schema

Digital Inputs




- (*) Type T fuse
- (A) Sink wiring (positive logic).
- (B) Source wiring (negative logic).

Connection of the Fast Inputs




10, 11, 16, 17

Transistor Outputs




- (*) Type T fuse
- (1) The V0+ and V1+ terminals are **not** connected internally.
- (2) The V0- and V1- terminals are **not** connected internally.


Connection of the Fast Outputs



Q0, Q1

Analog Inputs






The (-) poles are connected internally.

Pin	Wire Color
0 V	Black
AN1	Red
0 V	Black
AN0	Red


USB Mini-B Connection



15

Apr 25, 2024

SL1 Connection




SL1


Ν°	RS 232	RS 485
1	RxD	N.C.
2	TxD	N.C.
3	RTS	N.C.
4	N.C.	D1
5	N.C.	D0
6	стѕ	N.C.
7	N.C*.	5 Vdc
8	Common	Common

N.C.: not connected

 $[\]ensuremath{^*}$: 5 Vdc delivered by the controller. Do not connect.



SL2 Connection




Ν°	RS 485
1	N.C.
2	N.C.
3	N.C.
4	D1
5	D0
6	N.C.
7	N.C.
8	Common

N.C.: not connected

Performance Curves

Derating Curves


Embedded Digital Inputs (No Cartridge)



X: Ambient temperature

Y: Input simultaneous ON ratio

Embedded Digital Inputs (with Cartridge)




X: Ambient temperature

Y: Input simultaneous ON ratio

Derating Curves


Embedded Digital Outputs (No Cartridge)



X: Ambient temperature

Y: Output simultaneous ON ratio

Embedded Digital Outputs (with Cartridge)



X: Ambient temperature

Y: Output simultaneous ON ratio