# **Product data sheet**

Specification






Universal timing relay, Harmony Time, plug in, 0.1 s..60 mn, 24...240 V AC, 1 OC

RE88867105

! Discontinued on: Nov 22, 2021



Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Range Of Product	Zelio Time
Product Or Component Type	Universal timing relay
Discrete Output Type	Relay
Width Pitch Dimension	1.38 in (35 mm)
Component Name	RE88867
Time Delay Type	At B Ht Ac H D W Di A C
Time Delay Range	660 s 110 h 110 min 660 min 110 s 10100 h 0.11 s

## Complementary

Electrical Connection	Plug-in sub-base 8
Contacts Material	AgNi (cadmium free)
Line Rated Current	8 A
[Us] Rated Supply Voltage	24 V DC 24240 V AC 50/60 Hz
Voltage Range	0.851.1 Us
Housing Material	Self-extinguishing
Repeat Accuracy	+/- 0.5 % IEC 61812-1
Temperature Drift	+/- 0.05 %/°C
Voltage Drift	+/- 0.2 %/V
Setting Accuracy Of Time Delay	+/- 10 % of full scale 25 °C IEC 61812-1
Minimum Pulse Duration	100 ms under load 30 ms
Maximum Reset Time	100 ms on de-energisation

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

On-Load Factor	100 %
Maximum Power Consumption	32 VA 240 V
Maximum Power Consumption	0.6 W 24 V 1.5 W 240 V
Breaking Capacity	2000 VA
Breaking Capacity	80 W
Minimum Switching Current	10 mA
Maximum Switching Current	8 A
Maximum Switching Voltage	250 V
Electrical Durability	100000 cycles 8 A, 250 V resistive
Mechanical Durability	5000000 cycles
[Uimp] Rated Impulse Withstand Voltage	5 kV 1.250 μs IEC 60664-1 5 kV 1.250 μs IEC 61812-1
Marking	CE
Creepage Distance	4 kV/3 IEC 60664-1
Surge Withstand	1 kV differential mode IEC 61000-4-5 level 3 2 kV common mode IEC 61000-4-5 level 3
Local Signalling	for flashing: timing in progress LED indicator (green) for on steady: relay energised, no timing in progress LED indicator (green) for pulsing: relay energised, no timing in progress (except functions Di-D) LED indicator (green)
Net Weight	0.18 lb(US) (0.08 kg)

## **Environment**

10 ms
2.5 kV 1 mA/1 minute 50 Hz IEC 61812-1
IEC 60669-2-3
93/68/EEC
EN 50081-1/2
IEC 61812-1
EN 50082-1/2
73/23/EEC
89/336/EEC
CSA
cURus
GL
-4140 °F (-2060 °C)
-22140 °F (-3060 °C)
IP20 IEC 60529 terminal block)
IP40 IEC 60529 housing)
IP50 IEC 60529 front panel)
0.35 mm 1055 Hz)IEC 60068-2-6
93 % without condensation IEC 60068-2-3
6 kV in contact IEC 61000-4-2 level 3
8 kV in air IEC 61000-4-2 level 3
9.14 V/m (10 V/m) 80 MHz to 1 GHz ENV 50140/204 level 3
9.14 V/m (10 V/m) 80 MHz to 1 GHz IEC 61000-4-3 level 3
1 kV IEC 61000-4-4 level 3 capacitive connecting clip)
2 kV IEC 61000-4-4 level 3 direct)
10 V 0.1580 MHz)ENV 50141 (IEC 61000-4-6)

Immunity To Voltage Dips	30 % / 10 ms IEC 61000-4-11 60 % / 100 ms IEC 61000-4-11 95 % / 5 s IEC 61000-4-11
Disturbance Radiated/Conducted	Class B FN 55022 (FN 55011 group 1)

# Ordering and shipping details

Category	US10CP222370
Discount Schedule	0CP2
Gtin	3389110278576
Returnability	No
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.57 in (4 cm)
Package 1 Width	1.89 in (4.8 cm)
Package 1 Length	3.86 in (9.8 cm)
Package 1 Weight	2.65 oz (75 g)

# **Contractual warranty**

Warranty 18 months

# Sustainability Screen Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information


Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
<b>Environmental Disclosure</b>	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

## **Dimensions Drawings**

## Width 35 mm




## **Product data sheet**

## RE88867105

Connections and Schema

## Wiring Diagram



#### **Technical Description**

## Function A : Power on Delay Relay


#### Description

The timing period T begins on energisation. After timing, the output(s) R close(s). The second output can be either timed or instantaneous.

#### **Function: 1 Output**



#### **Function: 2 Outputs**



#### Function Ac: On- and Off-Delay Relay with Control Signal

#### **Description**


After power-up, closing of the control contact C causes the timing period T to start (timing can be interrupted by operating the Gate control contact G). At the end of this timing period, the relay closes.

When control contact C re-opens, the timing T starts.


At the end of this timing period T, the output reverts to its initial position (timing can be interrupted by operating the Gate control contact G).

The second output can be either timed or instantaneous.

#### **Function: 1 Output**




#### **Function: 2 Outputs**



## Function At: Power on Delay Relay (Summation) with Control Signal

#### Description

After power-up, the first opening of control contact C starts the timing. Timing can be interrupted each time control contact closes. When the cumulative total of time periods elapsed reaches the pre-set value T, the output relay closes.




T = t1 + t2 +...

## Function B : Interval Relay with Control Signal

#### Description

10


After power-up, pulsing or maintaining control contact C starts the timing T. The output R closes for the duration of the timing period T then reverts to its initial state.



## Function Bw : Double Interval Relay with Control Signal

#### Description

On closing and opening of control contact C, the output R closes for the duration of the timing period T.




## Function C : Off-Delay Relay with Control Signal


#### **Description**

After power-up and closing of the control contact C, the output R closes. When control contact C re-opens, timing T starts. At the end of the timing period, the output(s) R revert(s) to its/their initial state. The second output can be either timed or instantaneous.

#### **Function: 1 Output**



#### **Function: 2 Outputs**



## Function D : Symmetrical Flasher Relay (Starting Pulse Off)

#### Description


Repetitive cycle with two timing periods T of equal duration, with output(s) R changing state at the end of each timing period T.

The second output can be either timed or instantaneous.

#### **Function: 1 Output**



#### **Function: 2 Outputs**



## Function Di : Symmetrical Flasher Relay (Starting Pulse On)

#### **Description**

Repetitive cycle with two timing periods T of equal duration, with output(s) R changing state at the end of each timing period T.


The second output can be either timed or instantaneous.

## **Function: 1 Output**



#### **Function: 2 Outputs**

14



## Function H : Interval Relay


#### **Description**

On energisation of the relay, timing period T starts and the output(s) R close(s). At the end of the timing period T, the output(s) R revert(s) to its/their initial state. The second output can be either timed or instantaneous.

#### **Function: 1 Output**



#### **Function: 2 Outputs**



2 timed outputs (R1/R2) or 1 timed output (R1) and 1 instantaneous output (R2 inst.)

15

## Function Ht: Interval Relay (Summation) with Control Signal


#### **Description**

On energisation, the output R closes for the duration of a timing period T then reverts to its initial state.

Pulsing or maintaining control contact C will again close the output R.

Timing T is only active when control contact C is released and so the output R will not revert to its initial state until after a time t1 + t2 +...

The relay memorises the total, cumulative opening time of control contact C and, once the set time T is reached, the output R reverts to its initial state.



T = t1 + t2 +...

## Legend

	Relay de-energised
	Relay energised
	Output open
	Output closed
С	Control contact
G	Gate
R	Relay or solid state output
R1/R2	2 timed outputs
R2 inst.	The second output is instantaneous if the right position is selected
Т	Timing period
Та -	Adjustable On-delay
Tr -	Adjustable Off-delay
U	Supply